




HOCKMEYER

PROVIDING PROCESS SOLUTIONS AROUND THE WORLD

HCP IMMERSION MILL

Rapid recirculation and an aggressive shear zone for high-efficiency milling and tight particle-size distribution.

- Reduction of process time
- Reduction of raw material costs by maximizing development
- Minimal product loss with thorough, efficient & easy cleanup
- Multiple tank positions with 360-degree rotation
- Programmable control packages with a touchscreen display
- Various materials of construction available



PATENTS: 7,175,118, 7,559,439, 7,828,234, 7,883,036, 7,914,200, 8,182,133, 8,376,252, 8,733,677

Model	HP	BATCH SIZE Min/ Max (Gal.)	VESSEL (Diameter x Height)	MEDIA VOLUME (Liters)
Micromill	1	1.06/4.23 cups	4 x 7.5	49 mL
HCP - 1/4	2	1/5	8.3 x 12	0.25
HCP - 1	10	5/20	14 x 26	1
HCP - 1 M	10	3/15	12 x 19	1
HCP DM	20	40/55	24 x 37	2.5
HCP - 2.5	15	13/55	18 x 24	2.5
HCP - 10	40	50/150	32 x 42	8
HCP - 20	60	120/250	42 x 48	18
HCP - 40	100	250/600	48 x 54	35
HCP - 60	150	600/800	56 x 60	46
HCP - 80	200	800/1100	66 x 84	63